

Accessory Models: FFPFDT, FFPFSOA, FFPFRFV, FFPFFP

(For use with circulator models; FFPFWRC67S1U & FFPFWRC66B1S only)



FFPFDT - 7-Day Digital Timer

The digital, programmable timer allows for control of the circulator (on / off) at designated times (up to four custom settings per 24 hour period) for up to 7 days (similar to a programmable thermostat). The timer is plugged into a standard wall outlet and the circulator pump is then plugged into the timer allowing for time control of the pump. This unit has an internal battery backup which will, in the event of loss of AC power, power the unit and save / maintain program settings (battery will last for 48 hours before needing to be recharged).

NOTE: The Digital timer (FFPFDT) and Aquastat (FFPFSOA) can ALSO be used together, in tandem to allow for BOTH temperature AND time control.



FFPFSOA - Snap on Aquastat

The Aquastat simply "clips" onto any material 1/2" ID or 3/4" ID piping. It then plugs into a standard wall outlet. You would then plug in the power cord for the circulator into the aquastat plug and it will turn the circulator on and off automatically at fixed set points (ON 98°F and OFF at 114°F) allowing for temperature control of pump.

NOTE: The Digital Timer (FFPFDT) and Aquastat (FFPFSOA) can ALSO be used together, in tandem to allow for BOTH temperature AND time control.



FFPFRFV - Retro-Fit Valve

The thermostatic Lead-Free Bronze bypass valve is installed under the sink fixture furthest from the hot water heater. The valve reacts to the decreasing temperature in the hot water supply piping and "opens" to allow the flow back through the cold water piping (essentially using the cold water piping as the return line) and providing "instant" hot water at the fixtures.

NOTE: The Retro-Fit Valve (FFPFRFV) MUST be installed with Power-Flo Pumps Model FFPFWRC67S1U circulator pump.



FFPFFP - Copper Multi Fitting Pack

Pack includes;

Two (2) 1/2" SW x FNPT,

Two (2) 3/4" SW x FNPT,

Two (2) 3/4" SW x 1/2" SW Reducing Bushings,

Two (2) 3/4" Street Hub Copper Union

NOTE: Used with Flo Fab Pumps Model FFPFWRC66B1S circulator pump.